Product Specification

Material	28552.410
Material description	Tetrahydrofuran
Grade	GPR RECTAPUR stabilized with 0,025 to 0,04 % of BHT
CAS Number	109-99-9
Molecular formula	C4H8O
Molecular mass	72.11

Characteristics	Specifications
Assay	Min. 99 %
Stabilizer (BHT)	About 250 ppm
Appearance	Clear colourless liquid
IR Spectrum	Passes test
Boiling point	65.0 --> 66.5 °C
Density (20/4)	0.885 --> 0.888
Free acidity	Max. 0.0003 meq/g
n 20/D	1.406 --> 1.408
Peroxides (as H2O2)	Max. 100 ppm
Water	Max. 0.03 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare; France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.